

Infrared Radiation Source

JSIR350-4-AL-R-D6.0-0-0

Fast radiation source with reflector for use with thermopiles and pyroelectric detectors in NDIR gas analysis and other applications.

Spectral Output Range ¹	typ. 1 ... 20	µm
Active Area	2.2 x 2.2	mm ²
Hot Resistant	40±20	Ω
Temperature Coefficient	typ. 650	ppm/K
Time Constant	typ. 15	ms
Nominal Power Consumption	0.65	W
Operation Voltage ²	typ. 4.9	V
Operation Current ²	typ. 132	mA
Active Area Temperature ^{3,5}	640	°C
Window	-	
Mass	~1	g
Housing	T039 (modified)	
Lifetime ⁴	> 5,000 h at 740°C > 100,000 h at 640°C	

¹ without window

² with 40Ω

³ at nominal power (0.65W)

⁴ at 10 Hz, 50% duty cycle, preliminary results


⁵ at T_{amb} = 25°C



Pin Assignment

Bottom View

Pin 1 Power
Pin 2 Case
Pin 3 Power



Absolute Max. Ratings

Power 1.2 W

Housing temperature 200 °C

Active Area Temperature 850 °C

The current data are based on simulations and tests. They are subject to change during the next evaluation steps.

Micro-Hybrid Electronic GmbH





**Heinrich-Hertz-Straße 8
D-07629 Hermsdorf**

**Tel.: +49 366 01 592 100
Fax: +49 366 01 592 110**


**Email: Infrared@mico-hybrid.de
Web: www.mico-hybrid.de**

LIVING MICROWORLDS.

Infrared Radiation Source JSIR350-4-AL-R-D6.0-0-0



Housing




Optional parts

Window – For hermetic sealing and / or spectral narrowing of the radiation

Evaluation Kit – For independent evaluation of emitters and detectors

Operation range



Micro-Hybrid Electronic GmbH

**Heinrich-Hertz-Straße 8
D-07629 Hermsdorf**

**Tel.: +49 366 01 592 100
Fax: +49 366 01 592 110**

**Email: Infrared@mico-hybrid.de
Web: www.mico-hybrid.de**

LIVING MICROWORLDS.